

# product data sheet

## i.7 floor cleaner



### Properties

Ecological highly concentrated daily floor cleaner suitable for all water-resistant, hard floor surfaces.

Also ideal for sports floors and floors with a protective (polymer) coating.

#### **Better**

Smart dosing options (automatic dispenser, portable manual dosing, or ready-to-use) help prevent overdosing, reduce waste, and lower overall cleaning costs.

#### **Safer**

Non-classified and safe to use without protective equipment. Where industry or site-specific safety guidelines recommend the use of protective equipment, i-hygienic advises adhering to those recommendations.

#### **Greener**

Plant-based formula and bio-based packaging result in a net carbon-negative impact.

#### **Faster**

Performance-enhanced daily cleaner for quick and effective floor maintenance.

#### **Cleaner**

The optimal daily cleaning solution for all hard, water-resistant floors, including sports and coated surfaces.

# product data sheet

## i.7 floor cleaner

### Instructions for Use

Remove dust and loose dirt from the floor. Prepare the cleaning solution according to the dosage instructions in a mop bucket or in the tank of a floor cleaning machine. Clean the floor as usual. Mop, wipe, or vacuum up the solution, or use a floor squeegee to move it toward the drain. Allow the damp floor to air dry; rinsing is not necessary. For periodic cleaning or heavy soiling, apply the cleaning solution to the floor and let it work for about 5 minutes. In case of heavy soiling, the dosage may be doubled. After use of this cleaning product in the i-mop, drain the water tank, refill with fresh water, and clean the filters.

### Transport, Handling, and Storage

Non-classified product. No restrictions on handling, transport, or storage. See Safety Data Sheet (SDS) for detailed information.

### Dosage

Dosing protocol	AutoDose Ultra	FlexDose Ultra	FlexDose
Packaging	Pouch	Dispensing bottle	Dispensing bottle / Can
Standard min. dosing	5ml on 5ltr	5ml on 5ltr	10ml on 5ltr

### Specifications

Dosing protocol	AutoDose Ultra	FlexDose Ultra	FlexDose Ultra	FlexDose
Packaging (CU)	Pouch	Dispensing bottle	Can	Dispensing bottle
Content CU (litr)	1.8	2	5	1
Articlecode CU	I7.PO.1800	I7.DB.2000	I7.CA.5000	I7.DB.1000
Barcode CU	8721284400646	8721284400400	8719956069680	8721284400400
Articlecode box (BU)	K.4.I7.PO.1800	K.6.I7.DB.2000	K.2.I7.CA.5000	K.6.I7.DB.1000
Barcode BU	8721284400745	8721284400509	8719956069987	8721284400509
Content BU	4	6	2	6
BU per layer	12	15	16	14
Pallet layers	5	5	5	6
BU on pallet	60	30	80	84
CU on pallet	240	180	160	504
<b>Safety Data Sheet</b>	<a href="#">Download SDS</a>	<a href="#">Download SDS</a>	<a href="#">Download SDS</a>	<a href="#">Download SDS</a>